

## Wand Scanner



### MS100 Wand Scanner

The MS100 bar code wand is targeted toward low reading volume and cost effective solutions. The advanced optics and electronic design convert bar code labels into a high quality digital signal. Able to read color, faded and low contrast barcodes quickly and accurately, the MS100 is a proven solution.

Its shape gives the MS100 the comfort and handling of a conventional ink pen. Just sweep the tip of the wand across the bar code in either direction and listen for the "good read" beep that lets you know the data has been successfully captured. It doesn't get easier than that.

### Features

- Rugged, lightweight design
- Easy to use and configure
- Low power consumption
  - Wide read angle
  - High scan speed
- User configurable via PC programming
  - Advanced Data Editing
- Available with TTL, keyboard wedge RS232 and USB interfaces

### Optical

Light Source	650 ~ 660nm Red LED
Receiving Device	Photo Sensor
Depth of field	0.04" (1.0mm)
Resolution	5 mils (0.127mm)
Print Contrast	0.6 minimum
Scan Rate	4 ~ 24 inches/sec. (10 ~ 60 cm/sec)
Reading Angle	45° to 90°
Ambient Light	5000 Lux/Max

### Functionality

Symbologies	Code 39 standard and full ASCII, EAN-13, UPC-A, EAN-8, UPC-E, standard 2 of 5, Code 128, Code 93, MSI, Code 11, Code 32, Delta Code, Label Code, Plessey Code, Codabar
Interface	USB, Keyboard wedge, RS232, TTL (undecoded)

### Mechanical and Electrical

Dimensions:	Length 5.5 Inches (140mm) Diameter 1.2 x .9 Inches (30 x 23mm)
Weight:	76g
Cable	71 Inches (180 cm)
Case Material	ABS plastic
Supply Voltage	5V DC ± 10%
Surge Power	< 800mA
Working Current	60mA ± 10mA

### Environmental:

Operating Temperature	32°F to 122°F (0°C to 50°C)
Storage Temperature	-4°F to 140°F (-20°C to 60°C)
Humidity	20% to 85% RH non-condensing
Mechanical Shock	5 ft. (1.5 m) drop on concrete



#### Unitech America

Los Angeles, Houston, Guadalajara  
<http://www.ute.com> e-mail: [inquiry@ute.com](mailto:inquiry@ute.com)  
<http://latin.unitech-adc.com> e-mail: [info@latin.ute.com](mailto:info@latin.ute.com)

#### Unitech Asia Pacific

Taipei  
<http://www.unitech-adc.com> e-mail: [aidcsales@tw.ute.com](mailto:aidcsales@tw.ute.com)

#### Unitech Japan

Tokyo  
<http://www.unitech-japan.co.jp> e-mail: [sales@jp.ute.com](mailto:sales@jp.ute.com)

#### Unitech Europe

Tilburg / Netherlands  
<http://www.unitech-europe.com> e-mail: [sales@eu.ute.com](mailto:sales@eu.ute.com)

#### Unitech Greater China

Beijng, Shanghai, Guang Zhou, Xiamen  
<http://www.ute.com.cn> <http://www.ute.cn> [unitech@cn.ute.com](mailto:unitech@cn.ute.com)  
 Taipei <http://adc-utt.unitech.com.tw> [barcode@tw.ute.com](mailto:barcode@tw.ute.com)

#### Head Office

Taipei  
<http://www.unitech-adc.com> e-mail: [marketing@tw.ute.com](mailto:marketing@tw.ute.com)